



## DYNAMIC ADJUSTABLE ANGLE BACK CANE INTERFACE SET

This device was designed for users who display strong extensor spasticity of the back leading to ongoing breakage of wheelchair back canes and mounts. This device absorbs and diffuses tone during extension and aids to gradually return the client to a preferred upright seating position.

- Adjustable seat-back angle mounting bracket positions of 90, 100, or 110 degrees
- Provides resistance by attachment of up to four 40lb, 60lb, 80lb, or 120lb gas struts (two per back cane)
- Lock-out position for seat-back at 90, 100, or 110 degree angle
- Up to 30 degrees of extension in full range of motion position
- ROM can be limited to 0-15 degrees or 15-30 degrees of travel from preferred seat-back angle
- Bracket mounts to 1" OD tube frames
- Uses OEM 1" back canes (\*may require some cutting/drilling)

### Miller's Dynamic Adj-Ang Back Cane Interface Set

HCPC: K0108

- **49440** (Dynamic Adj-Ang Back Cane Interface,40lb,Set)
- **49460** (Dynamic Adj-Ang Back Cane Interface,60lb,Set)
- **49480** (Dynamic Adj-Ang Back Cane Interface,80lb,Set)
- **49412** (Dynamic Adj-Ang Back Cane Interface,120lb,Set)

Please contact our sales staff to assist you in placing an order for any of our products or to answer any questions that you may have. If you can't find what you need in our product catalog or on our website, we can work with you to create a custom solution.



***We specialize in creating solutions to expand your capabilities!***

2023 Romig Rd. Akron, OH 44320  
Toll Free (800)837-4544  
Fax (866)572-2603  
**MillersAdaptive.com**